



# Lowest overall running costs and highest output!

## MASTER PL-T Xtra 4 Pin

MASTER PL-T Xtra is an efficient compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications demanding higher lighting levels. MASTER PL-T Xtra lamps furthermore provide significantly lower operating costs thanks to their lifetime, which is more than double that of a standard MASTER PL-T lamp, and their very low early failure rate. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 4-pin version is designed for operation on electronic gear and is provided with a plug-in/pull-out lamp base.

### Benefits

- Extra long life
- Longer lifetime and less early failures lead to less hassle and lower maintenance costs and facilitate the change from spot to group replacement
- Optimal light performance for long operation per switch-on
- More light (about 15% more) per light point than common

### Features

- 4-pin base
- Philips bridging technology applied
- Extra long lifetime and less early failures
- Fluorescent tri-phosphor technology
- Low light depreciation over lamp life
- Fast light run-up

# MASTER PL-T Xtra 4 Pin

## Application

- Designed for general or supplementary lighting in professional and semi-professional environments
- Ideal for use in recessed or surface mounted downlighters, wall units, outdoor lighting
- Suitable for use in applications where maintenance costs are high (high ceilings, difficult to reach): department stores, supermarkets, warehouses, production halls and public areas

## Warnings and Safety


- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

## Versions



LPPR PLT4PLTG 42W

## Dimensional drawing



Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T Xtra 42W/840/4P 1CT/ 5X10BOX	41.0 mm	120.7 mm	145.0 mm	160.7 mm

## MASTER PL-T Xtra 4 Pin

