



MSR Gold™ FastFit – easy lamp replacement in seconds

MSR Gold™ FastFit

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR GoldTM 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

Benefits

- · Lamp replacement in just seconds, exchangeable with halogen lamp
- · High beam intensity
- \cdot Easy handling, smaller and lighter fixtures possible
- · Boostable light levels
- Enables use at higher temperatures in any burning position. Longer lifetime, fewer early failures, consistent performance over time
- · Reduces early lamp or lamp holder failures. Excellent current transfer
- Pure, white light; colour point close to black body line

MSR Gold™ FastFit

Features

- Philips FastFit
- · Very short arc
- Compact design
- · Flexible power range
- · Philips pinch protection
- · Innovative gold plated pins
- · MSR filling

Application

Entertainment

Warnings and Safety

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions








XPPR_XDMSR_0021-Product photo


Dimensional drawing



Product	D (max)	0	L (min)	L (max)	L	C (max)	F
MSR Gold 1500 FastFit	28 mm	6.3 mm	64 mm	66 mm	65 mm	128 mm	50 mm
1CT/4							

MSR Gold™ FastFit

Dimensional drawing



·	
General Information	
Cap-Base	PGJX50
Operating Position	UNIVERSAL
Controls and Dimming	
Dimmable	Yes

Product	D (max)	0	L (min)	L (max)	L	C (max)	F
MSR Gold 1200 FastFit 1CT/4	26.1 mm	5.5 mm	64 mm	66 mm	65 mm	128 mm	50 mm
MSR Gold 700 FastFit 1CT/4	23.2 mm	3.8 mm	64 mm	66 mm	65 mm	112 mm	50 mm
MSR Gold 700/2 FastFit 1CT/8	23.2 mm	3.8 mm	64 mm	66 mm	65 mm	112 mm	50 mm

Light Technical

		Correlated Color	Color		
	Full Product	Temperature	rendering	Color	Luminous
Order Code	Name	(Nom)	index (CRI)	Code	Flux
928107305115	MSR Gold 1500	6000 K	80	-	119,550 lm
	FastFit 1CT/4				
928106005115	MSR Gold 700	6000 K	79	-	54,000 lm
	FastFit 1CT/4				

		Correlated Color	Color		
	Full Product	Temperature	rendering	Color	Luminous
Order Code	Name	(Nom)	index (CRI)	Code	Flux
928106205114	MSR Gold 700/2	7500 K	73	2	46,000 lm
	FastFit 1CT/8				
928175005115	MSR Gold 1200	6000 K	80	-	92,000 lm
	FastFit 1CT/4				

Operating and Electrical

			Lamp Current	
Orde	er Code	Full Product Name	(Nom)	Power Consumption
9281	07305115	MSR Gold 1500 FastFit 1CT/4	15.3 A	1,500 W
9281	06005115	MSR Gold 700 FastFit 1CT/4	10.2 A	700 W

		Lamp Current	
Order Code	Full Product Name	(Nom)	Power Consumption
928106205114	MSR Gold 700/2 FastFit 1CT/8	10.2 A	700 W
928175005115	MSR Gold 1200 FastFit 1CT/4	15 A	1,200 W



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.