



TUV PL-L - Compact solution for professional applications

TUV PL-L

TUV PL-L lamps are compact UVC (germicidal) lamps used in professional water and air disinfection units. The compact size of the lamp allows for a small system design and design flexibility. TUV PL-L lamps offer almost constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy. Thanks to the single-ended lamp base, lamp replacement is easy.

Benefits

- · Security of effective disinfection over the useful lifetime of the lamp
- High system efficacy because it is not required to over-design the purification system to maintain effectiveness of disinfection

Features

- · Short-wave UV radiation with a peak at 253.7 nm (UVC) for disinfection purposes
- $\boldsymbol{\cdot}$ Protective inside coating ensures constant UV output over the complete lifetime of the lamp
- $\boldsymbol{\cdot}$ Special lamp glass filters out the 185 nm ozone-forming radiation
- High Output versions contain wind-chill correction for improved performance in moving air and reducing amount of required lamps
- High Output versions for optimum UVC output per lamp length, allowing for reduction of system size
- · Warning sign on lamp indicates that the lamp radiates UVC


Application

- \cdot Deactivation of bacteria, viruses and other micro-organisms
- · Residential drinking water units
- · Fish pond and process water units
- · In-duct air treatment units
- · Stand alone air purifiers
- · Air disinfection systems in for example hospitals, universities and laboratories

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.

Dimensional drawing



Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
TUV PL-L 35W/4P HO 1CT/25	18 mm	39 mm	195 mm	220 mm	225 mm
TUV PL-L 60W/4P HO 1CT/25	18 mm	38 mm	390 mm	415 mm	420 mm
TUV PL-L 95W/4P HO 1CT/25	18 mm	38 mm	505 mm	530 mm	535 mm

General Information		
Cap-Base	2G11	
Approval and Application		
Mercury (Hg) Content (Nom)	4.4 mg	

Operating and Electrical

		Lamp Current	
Order Code	Full Product Name	(Nom)	Power Consumption
927904204007	TUV PL-L 35W/4P HO 1CT/25	0.85 A	35 W
927909004007	TUV PL-L 60W/4P HO 1CT/25	0.800 A	67 W

		Lamp Current	
Order Code	Full Product Name	(Nom)	Power Consumption
927909804007	TUV PL-L 95W/4P HO 1CT/25	0.8 A	90 W

TUV PL-L



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.