



Product Description

Actinic BL TL-E

Circular low-pressure mercury vapour fluorescent lamps

Benefits

- Perfectly matches the eye sensitivity of houseflies and in this way attracts more insects
- Safe for use
- Good environmental choice
- Design freedom

Features

- Emit long-wave UV-A radiation in the 350 – 400 nm range
- UV-B/UV-A ratio less than 0.1% (UV-B: 280 – 315 nm)

Application

- Photopolymerisation processes
- Reprography
- Insect traps

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Actinic BL TL-E

Versions



XPPR_XURTLE_0001-Product photo

Dimensional drawing



Product	D (max)	D (min)	F (max)	F (min)	E (min)	E (max)
Actinic BL TL-E 22W/10 1CT/20	30.9 mm	26.2 mm	155.6 mm	149.1 mm	205.0 mm	213.5 mm

